

AVerVision150 *Portable Document Camera*

Essence of Value!

- **3.2 mega pixel resolution**
- **8X total zoom**
- **Vivid live video quality with high-speed 24 fps**
- **Image capture and USB camera capabilities**
- **Detachable LED light module**



Product Specifications & Features

Image / Video

Image Sensor	1/2" CMOS
Pixel	3.2 Mega Pixel
Zoom	Total: 8X (2X AVERZOOM™ + 4X Digital Zoom)
Frame Rate	24 fps (Max.)
Focus	Manual
Shooting Area	360mm x 270mm
Image Rotation	0°/ 90°/ 180°/ 270°
Image Capture	Built-in Memory (Max: 32)
Image Effect	Color/ B/W/ Negative/ Freeze
White Balance	Auto/ Manual
Exposure	Auto/ Manual
Night View	Manual
Display Mode	Text/ Graphics/ High Frame
Flicker Filter Control	2 Levels

Input / Output / Lighting

VGA Input	15-Pins D-sub, Active pass through
VGA Output	XGA (1024 x 768)
S-Video, Composite Video Output	NTSC or PAL
USB Port	USB1.1
Power Supply	DC 12V
Power Source	AC 100-240V, 50-60 Hz
Light Source	LED module
Warranty	2 Year Limited Parts and Labor *1
Certification	FCC, CE

Software System Requirement

Windows®	2000 / XP
Macintosh®	OS 10.3 (Panther) OS 10.4 (Tiger)

Dimension

Dimension	Setup: 220mm x 140mm x 570mm Folded: 380mm x 170mm x 55mm
Net Weight	2kg (about 3.8lb)

3.2 Mega Pixel CMOS sensor



410K Pixel



3.2 Mega Pixel

Image capture and USB camera capabilities



AVerVision Application Software

Minimum System Requirement

For PC

- Pentium/ AMD class processor
- Windows2000 Professional with Service Pack 4, Windows XP Professional Service Pack 2 or Home
- 128 MB of RAM (256 MB recommended)
- 60 MB of available hard-disk space

For MAC

- PowerPC G4 1.25GHz
- Mac OS 10.3 (Panther), or 10.4 (Tiger)
- 256 MB of RAM



Package Content

Standard

- AVerVision150 Unit
- Power Adapter & Power Cord
- VGA Cable
- S-Video Cable
- USB Cable
- RCA Cable
- User Manual
- AVerVision Software CD
- LED Module without Laser Positioning Pointer
- Anti-glare Sheet
- Warranty Card

Optional

- Microscope Adapter
- Light Box
- Carrying Bag
- LED Module with Laser Positioning Pointer



Carrying Bag



Microscope Adapter




LED Module with/without Laser Positioning Pointer



Light Box

Back Panel



Side Panel



*1 Please refer to user manual

*2 Features subject to change without notice

International: (Tel) 886-2-2226-3630 (Fax) 886-2-2226-8751
 USA: (Tel) 1-408-263-3828 (Fax) 1-408-263-8132
 U.K.: (Tel) 44-870-224-7116 (Fax) 44-44-870-224-7124
 Germany: (Tel) 49 (6074) 40740-0 (Fax) 49 (6074)40740-37
 France: (Tel) 01 60 05 75 16 (Fax) 01 60 05 78 42
 Spain: (Tel) 34-91-804- 6035 (Fax) 34-91-803-7629
 Thailand: (Tel) 66-2-9429262 (Fax) 66-2-9429266
 China: (Tel) 86-21-52987988 (Fax) 86-21-52987970
 Taiwan: (Tel) 886-2-2226-3630 (Fax) 886-2-2226-8751