



MD 421 II Dynamic Microphone

The MD 421 II is one of the best known microphones in the world. Its excellent sound qualities enable it to cope with the most diverse recording conditions and broadcasting applications. The five position bass control enhances its 'all-round' qualities. Color: black, sound inlet basket: black.

Features—Benefits

- Glass composite housing and hardened stainless steel basket—rugged and durable
- Five position bass roll-off switch—compensates for proximity effect
- Effective feedback rejection
- Clear sound reproduction
- Easy handling due to pronounced directivity
- Acoustic components enclosed in inner chassis—reduced sensitivity to dust and humidity
- Internal bass tubes—accurate low end response
- Handles exceptionally high sound pressure

Technical Data

Pick-up pattern	cardioid
Frequency response	30–17,000 Hz
Sensitivity (free field, no load) (1 kHz)	2 mV/Pa ± 3 dB at 1 kHz, nominal
Nominal impedance	200 Ω
Min. terminating impedance	200 Ω
Dimensions in inches	8.46 x 1.8 x 1.92
Weight approx.	13.58 oz

Supplied Accessories

1 lock-on stand adapter	MZA 421
-------------------------	---------

Optional Accessories

Grey foam windscreen	MZW 421
21' XLR microphone cable	MC21N
Shockmount	MZS 421

Architect's Specifications

The unit shall be a cardioid studio microphone, with five-position bass control. The frequency response shall be 30–17,000 Hz, with sensitivity of (free field, no load) 2 mV/Pa ± 3 dB at 1 kHz. The nominal impedance shall be 200 Ω. The min. terminating impedance shall be 200 Ω. The dimensions shall be 8.46 x 1.8 x 1.92 inches, and weight approx. 13.58 oz. The unit shall be a Sennheiser MD 421 II.

Sennheiser Electronic Corporation, 1 Enterprise Drive, Old Lyme, CT 06371

Telephone: 860-434-9190 • Fax: 860-434-1759 • Web: <http://www.sennheiserusa.com>

Sennheiser Mexico: Av. Xola 613, PH6, Col. Del Valle 03100, Mexico, DF. Telephone: (525) 639-0956. Fax: (525) 639-9482

Sennheiser Canada: 221 Labrosse Ave, Pte-Claire, PQ H9R 1A3. Telephone: 514-426-3013. Fax: 514-426-3953

Manufacturing Plant: Am Labor 1, 30900 Wedemark, Germany